

Push-On Fittings



Dixon™ push-on fittings are intended for use with Lok-On (push-on style) hose only. No hose clamps or ferrules are needed. Push-On fittings will properly grip Lok-On hose only when pushed all the way in, with the cut end of the hose completely concealed by the plastic cap.

Rigid Tube x Push-On Hose Barb



Hose ID	Tube OD	Brass		303 Stainless		Opt Qty
		Part #	Price/E	Part #	Price/E	
1/4"	3/16"	294-0403	\$4.32	---	---	100
1/4"	1/4"	294-0404	2.93	294-0404SS	\$30.86	100
1/4"	5/16"	294-0405	4.00	---	---	100
3/8"	3/8"	294-0606	3.32	294-0606SS	28.57	50
1/2"	1/2"	294-0808	4.92	294-0808SS	33.06	50
5/8"	5/8"	294-1010	7.28	---	---	25
3/4"	3/4"	294-1212	11.29	294-1212SS	38.67	25

Push-On Hose Menders



Hose ID	Brass		303 Stainless		Opt Qty
	Part #	Price/E	Part #	Price/E	
1/4"	BPM2	\$3.00	SSPM2	\$34.37	100
5/16"	BPM25	3.72	---	---	100
3/8"	BPM3	3.40	SSPM3	39.28	50
1/2"	BPM4	5.50	SSPM4	43.61	50
5/8"	BPM5	7.86	---	---	20
3/4"	BPM6	9.25	---	---	15
1"	BPM8	16.15	---	---	10

Push-On Caps



Hose ID	Part #	Price/E	Pkg Qty
1/4"	2720400W	\$0.14	100
5/16"	2720500W	0.13	100
3/8"	2720600W	0.18	100
1/2"	2720800W	0.22	100
5/8"	2721000W	0.23	50
3/4"	2721200W	0.29	50
1"	2721600W	4.31	25

- Sold in package quantities only.

Tool for Push-On Fittings



Features:

- cuts push-on style hose and inserts the fitting
- Built-in cutter slices through 1/4" - 3/4" ID reinforced push-on hose without fraying.
- Clamp hose into tools vice and apply light pressure on handle to drive in the fitting.
- tool has four 7/16" diameter mounting holes for bench mounting
- overall size is 13 1/2" long x 2-3/8" wide x 7" height

Size	Part #	Price/E
1/4" - 3/4"	270AT	\$1143.00

Assembly Instructions:

1. Trim hose end with smooth square cut
2. Lubricate either push-on fitting, hose or both.
3. Insert push-on fitting into hose until first barb is in hose.
4. Place end of fitting against a flat object (bench, wall, etc.) and grip the hose one inch from end. Push with a steady force until end of hose is covered by yellow plastic cap.

Disassembly Instructions:

1. Leaving push-on fitting in place, make a 1" cut in the hose along the barbed end of the fitting. Note: Be careful not to nick barbs when cutting the hose.
2. With firm grip on hose, give a sharp downward pull to release the fitting from the hose.



Caution: Push-on fittings will properly grip push-on hose only when pushed all the way in, with the cut end of the hose completely concealed by the plastic cap.

Hose Assembly Tool



- installs 1/4", 5/16" and 3/8" hose fittings
- lightweight, portable, comfortable cushioned grip
- economical

Part #	Price/E
HHCI	\$222.00